



DPN 760 from Romaco Noack

Over 600 Romaco Noack DPN 760 machines in operation worldwide are proof of the confidence users in the prescription drugs, generics and contract sectors place in Noack technology. The flexibility of the intermittent motion Romaco Noack DPN 760 provides for both operation on a stand-alone basis or in line with a cartoner.

As a compact, entry-level solution, it is ideal for start-up operations but also offers a number of upgrade options to increase productivity. Its proven technology has been continually enhanced to serve the changing needs of the marketplace, establishing the next generation Romaco Noack DPN 760 as a key choice within the contract and generic markets, where fast changeover, reliability and high availability are essential.

Highlights

- Extremely simple and repeatable operation
- Very small footprint
- Processes all common thermoformable and alu cold forming films
- Powerful PLC with operator-friendly HMI
- Upgrade options include: automatic feeding systems, filling inspection and ejection station, inline foil printer, print mark registration and complete line with a cartoner and end of line equipment

Technical Data

Noack DPN 760

| | |
|--|-----------------------|
| Output blister/minute max. | 200 |
| Blister rows max. | 4 |
| Forming cycles/minute max. | 50 |
| Cutting cycles/minute max. | 50 |
| Foil width max., in mm | 165 |
| Forming area max., in mm | 155 x 138 |
| Forming depth max., in mm | 25 |
| Forming foil reel diameter max., in mm | 600 |
| Lidding foil reel diameter max., in mm | 250 |
| Machine dimensions (L x W x H), in mm | 3,150 x 1,350 x 1,700 |
| Weight, in kg | 1,500 |

